



THE DATASHEET OF 5001





Technical Data Sheet

3M™ Scotch-Weld™ Light Activated Epoxy Adhesive 5001 Clear



[Regulatory Info/SDS](#)

Product Description

3M™ Scotch-Weld™ Light Activated Epoxy Adhesive 5001 Clear is a one-part epoxy exhibiting a UV or blue-light activated cure with long room temperature pot life and low viscosity.

Product Features

- One-part adhesive
- UV and blue light activated cure
- Great depth of cure
- Low viscosity
- Excellent adhesion to glass, epoxy and aluminum

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Uncured Physical Properties

Attribute Name	Test Method	Value
Color		Clear
Components		1-Part
UV Tracer		No
Density - Liquid		1.11 g/mL ¹
Pot Life	ASTM D7867	4 weeks ²
Halogens (Cl, Br)		Representative samples have been tested and meet the chlorine and bromine content requirements of IEC 61249-2-21 ³

¹ Measured by Helium gas pycnometer at 23°C

² Determined by meeting minimum application viscosity requirements of the adhesive over time @ 23°C

³ Per IEC 61249-2-21

Temperature: 25 °C

Test Method: ASTM D7867

Attribute Name	Test Condition	Value
Viscosity - Cone and Plate	0.1 Hz	23 Pa·s ¹
Viscosity - Cone and Plate	1 Hz	11 Pa·s ¹
Viscosity - Cone and Plate	10 Hz	8 Pa·s ¹
Thixotropic Index	0.1 Hz / 1 Hz	3.2 ¹
Thixotropic Index	1 Hz / 10 Hz	1.4 ¹

¹ 40mm, 2.0°, 50um truncation cone and Peltier plate. 60s pre-shear at 100 Hz. 5 min flow ramp from 0.01 to 100 Hz @ 25°C

Typical Cure Profiles

Activate with 450nm light at 360mW/cm² for 2 seconds.

Temperature: 25 °C

Test Method: ASTM D4473

Attribute Name	Value
Time to Double Complex Viscosity	14 s ¹
Time to 1,000 Pa.s Complex Viscosity	2.1 min ¹
Time to 0.1 MPa Storage Modulus	24 min ¹
Time to 1 MPa Storage Modulus	2.5 h ¹
Time to 80% Storage Modulus Max	10 h ¹

¹ Parallel Plate Rheometer: Isothermal - 25mm parallel plate, 1 Hz. 450nm light, 360 mW/cm² for 2 seconds

Rate of overlap shear strength build after light activation (450nm; 360mW/cm² for 2 seconds).

Substrate: Etched Aluminum

Temperature: 23 °C (73 °F)

Test Method: ASTM D1002, ISO 4587

Attribute Name	Value
Time to Handling Strength	< 5 min ¹
Time to 80% Strength	4 h ²
Time to Full Strength	24 h ³
Overlap Shear Strength	12 MPa (Mixed Mode Failure) ⁴

¹ 2mm thick substrate. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to consistent >50 psi (0.34 MPa) overlap shear strength after light exposure (450nm light, 360 mW/cm² for 2 seconds).

² 2mm thick substrate. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to 80% of maximum overlap shear strength after light exposure (450nm light, 360 mW/cm² for 2 seconds).

³ 2mm thick substrate. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to maximum overlap shear strength after light exposure (450nm light, 360 mW/cm² for 2 seconds).

⁴ 2mm thick substrate. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to consistent >50 psi (0.34 MPa) overlap shear strength after light exposure (450nm light, 360 mW/cm² for 2 seconds).

Fast cure with 450nm light at 500mW/cm² for 15 seconds.

Temperature: 25 °C

Test Method: ASTM D4473

Attribute Name	Value
Time to 1,000 Pa.s Complex Viscosity	18 s ¹
Time to 0.1 MPa Storage Modulus	1 min ¹
Time to 1 MPa Storage Modulus	2.5 min ¹
Time to 80% Storage Modulus Max	1.7 h ¹

¹ Parallel Plate Rheometer: Isothermal - 25mm parallel plate, 1 Hz. 450nm light, 500 mW/cm² for 15 seconds

Rate of overlap shear strength build after fast cure dose (450nm; 500mW/cm² for 15 seconds).

Substrate: Soda-lime Glass

Temperature: 23 °C (73 °F)

Test Method: ASTM D1002, ISO 4587

Attribute Name	Value
Time to Handling Strength	Less than 5 min ¹
Time to 80% Strength	30 min ²
Time to Full Strength	1 h ³
Overlap Shear Strength	>10 MPa (Substrate Failure) ⁴

¹ 6mm thick substrates. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to consistent >50 psi (0.34 MPa) overlap shear strength after light exposure (450nm light, 500 mW/cm² for 15 seconds).

² 6mm thick substrates. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to 80% of maximum overlap shear strength after light

exposure (450nm light, 500 mW/cm² for 15 seconds).

- ³ 6mm thick substrates. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Time to maximum overlap shear strength after light exposure (450nm light, 500 mW/cm² for 15 seconds).
- ⁴ 6mm thick substrates. Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Overlap shear strength 24 hours after light exposure (450nm light, 500 mW/cm² for 15 seconds).

Depth of Cure

Temperature: 25 °C

Value
14 mm ¹
4.8 mm ²
2.3 mm ³

- ¹ Liquid adhesive is dispensed to fill a 7mm diameter cylindrical rubber sleeve. The adhesive is then exposed to 450nm light at 500 mW/cm² for 3 minutes at one side of the sleeve. The sample is heat accelerated at 65°C for one hour. The solidified portion of the adhesive is then removed from the rubber sleeve 1 hour after light exposure. The depth of cure is reported as the thickness of the solidified portion measured using a digital caliper.
- ² Liquid adhesive is dispensed to fill a 7mm diameter cylindrical rubber sleeve. The adhesive is then exposed to 450nm light at 500 mW/cm² for 15 seconds at one side of the sleeve. The sample is heat accelerated at 65°C for one hour. The solidified portion of the adhesive is then removed from the rubber sleeve and the depth of cure is reported as the thickness of the solidified portion measured using a digital caliper.
- ³ Liquid adhesive is dispensed to fill a 7mm diameter cylindrical rubber sleeve. The adhesive is then exposed to 450nm light at 360 mW/cm² for 2 seconds at one side of the sleeve. The sample is heat accelerated at 65°C for one hour. The solidified portion of the adhesive is then removed from the rubber sleeve and the depth of cure is reported as the thickness of the solidified portion measured using a digital caliper.

Typical Cured Characteristics

Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
Density - Cured Solid	ASTM D1875	1.16 g/mL ¹
Volume Shrinkage	ASTM D1875	4.1 % ¹
Peak Stress	ASTM D638, ISO 527	34 MPa ²
Young's Modulus	ASTM D638, ISO 527	1,920 MPa ³
Poisson's Ratio	ASTM D638, ISO 527	0.4 ³
Toughness	ASTM D638, ISO 527	4.2 J/m ³ ³
Elongation at Break	ASTM D638, ISO 527	11 % ³
Shore D Hardness	ASTM D2240	65 ⁴
Notched Izod Impact	ASTM D256-10	50 J/m ⁵

- ¹ Measured by Helium gas pycnometer. Cured with 450nm light at 500mW/cm² for 3 minutes.
- ² Cured with 450nm light at 500mW/cm² for 3 minutes. 0.5mm film conditioned for >5 days in 23°C/50%RH. Die cut type IV dog bone. 100mm/min pull rate. Digital Image Correlation (DIC) used for strain measurements.
- ³ Cured with 450nm light at 500mW/cm² for 3 minutes. 0.5mm film conditioned for >5 days in 23°C/50%RH. Die cut type IV dog bone. 100mm/min pull rate. Digital Image Correlation (DIC) used for strain measurements.
- ⁴ 1 mm films stacked to 6 mm. Cured with 450nm light at 500mW/cm² for 3 minutes.
- ⁵ 3 mm thick sample. Cured with 450nm light at 500mW/cm² for 3 minutes.

Attribute Name	Test Method	Temperature	Test Condition	Value
Storage Modulus: DMA Temp Ramp	ASTM D4065	-20 °C (-4 °F)	1 Hz	2,700 MPa ¹
Storage Modulus: DMA Temp Ramp	ASTM D4065	0 °C	1 Hz	2,400 MPa ¹
Storage Modulus: DMA Temp Ramp	ASTM D4065	25 °C	1 Hz	1,900 MPa ²
Storage Modulus: DMA Temp Ramp	ASTM D4065	45 °C	1 Hz	900 MPa ³

Attribute Name	Test Method	Temperature	Test Condition	Value
Storage Modulus: DMA Temp Ramp	ASTM D4065	65 °C	1 Hz	50 MPa ³
Storage Modulus: DMA Temp Ramp	ASTM D4065	85 °C	1 Hz	13 MPa ³
Tg: DMA Temp Ramp	ASTM D7028		1 Hz	62 °C ¹
Storage Modulus: DMA Master Curve	ASTM D4065	25 °C	0.1 Hz	1,500 MPa ⁴
Storage Modulus: DMA Master Curve	ASTM D4065	25 °C	1 Hz	1,600 MPa ⁴
Storage Modulus: DMA Master Curve	ASTM D4065	25 °C	10 KHz	1,900 MPa ⁴

¹ Cured with 450nm light at 500mW/cm² for 3 minutes. 0.5mm film conditioned for >5 days in 23°C/50%RH (CTH). 1Hz film tension DMA Heat from -20°C to 100°C at 3°C/min. Tg reported as peak of Tan Delta.

² Cured with 450nm light at 500mW/cm² for 3 minutes. 0.5mm film conditioned for >5 days in 23°C/50%RH (CTH). 1Hz film tension DMA Heat from -20°C to 100°C at 3°C/min. Tg reported as peak of Tan Delta.

³ Cured with 450nm light at 500mW/cm² for 3 minutes. 0.5mm film conditioned for >5 days in 23°C/50%RH (CTH). 1Hz film tension DMA Heat from -20°C to 100°C at 3°C/min.

⁴ 0.5mm film conditioned for >5 days in 23°C/50%RH (CTH). Multi-frequency incremental temperature sweep film tension DMA Heat from -20°C to 100°C.

Typical Performance Characteristics

Overlap Shear Strength

Temperature: 23 °C (73 °F)

Test Method: ASTM D1002, ISO 4587

Substrate	Value
Etched Aluminum	14 MPa (Mixed Adhesive Failure) ¹
Stainless Steel	4.1 MPa (Adhesive Failure) ²
FR-4	17 MPa (Mixed Adhesive Failure) ³
PC/ABS Glass-filled	5.2 MPa (Mixed Adhesive Failure) ³
PC/Siloxane	2.7 MPa (Adhesive Failure) ³
PBT Glass-filled	3.2 MPa (Adhesive Failure) ³
Polyamide Glass-filled	4.8 MPa (Adhesive Failure) ³
Soda-lime Glass	>10 MPa (Substrate Failure) ³

¹ Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Pull rate: 10 mm/min. Tested 72 hours after light exposure (450nm light at 360 mW/cm² for 2 sec)

² Bond dimensions: 12.7mm x 25.4mm x 0.15mm. Pull rate: 10 mm/min. Substrate grit blasted with AC130-2 3M Surface Treatment Solution. Tested 72 hours after light exposure (450nm light at 360 mW/cm² for 2 sec)

³ Bond dimensions: 6.35mm x 25.4mm x 0.15mm. Pull rate: 10 mm/min. Tested 72 hours after light exposure (450nm light at 360 mW/cm² for 2 sec)

Electrical and Thermal Properties

Attribute Name	Test Method	Temperature	Test Condition	Value
Dielectric Strength	ASTM D149	25 °C		38 kV/mm ¹
Volume Resistivity	ASTM D1257	23 °C (73 °F)	500 V, 60 s	3.4x10 ¹⁴ Ω-cm

¹ Measured at 0.26 mm

Handling/Application Information

Directions for Use

For opaque substrates: Activate cure with 450nm light source at 360mW/cm² for 2 seconds and close bond in less than 5 seconds.

For transparent substrates: Adhesive can be fast cured at 450nm with 500mW/cm² for 15 seconds.

Application Techniques

- Dispensing
- Molding

Application Examples

- Mobile device bonding
- Wearable electronic device bonding
- Electronic Assembly
- Encapsulation

Storage and Shelf Life

Store product at 0°C to 4°C (32°F to 39.2°F) in the original, unopened packaging. For best performance, use this product within 12 months from date of manufacture.

Available Sizes

Attribute Name	Value
Packaging	30 mL syringe, 591 mL cartridge

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is commercially available from 3M. The commercially available product will have a COA specification established. The COA contains the 3M specifications and test methods for the products performance limits that the product will be supplied against. The 3M product is supplied to 3M COA test specifications and the COA test methods. Contact your local 3M representative for this product's COA.

This technical data sheet may contain preliminary data and may not match the COA specification limits and/or test methods that may be used for COA purposes.

Automotive Disclaimer

Select Automotive Applications:

This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the

applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

Warranty, Limited Remedy, and Disclaimer

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Experimental Product: This 3M product is an experimental or developmental product that has not been introduced or commercialized for general sale, and its formulation, performance characteristics and other properties, specifications (if any), availability, and pricing are not guaranteed and are subject to change or withdrawal without notice.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

3M is a trademark of 3M Company
©3M 2024 (10/24)

Looking for pricing, stock, or lifecycle information?

Click below to explore more details on WIN SOURCE:

 [View 5001](#) on WIN SOURCE

 [3M](#) Information

Optimize Your Supply Chain with WIN SOURCE Solutions

-  Global Sourcing Solution
-  Obsolete Management
-  Cost Control Management
-  Shortage Management
-  Alternative Solution
-  Excess Inventory Management